



# HOLOGRAPHIC

## SPECIFICATIONS

Composition	Average Thickness	Carrier	Certifications
Hologram Skin	105 microns	Adhesive polyester	REACH compliant  

## APPLICATION INSTRUCTIONS | Laser friendly

Applies on	SUGGESTED CUTTING SETTINGS			TRANSFER SETTINGS			
cotton, polyester, poly/cotton blends (not suited for treated and dye sublimated textiles)	Blade	Pressure	Speed	Time	Temperature	Pressure	Peel
	45°	from 90gf with a knew knife - 130gf used knife	20 cm/sec	15 seconds	155°C (311°F)	Medium (2,5/3,5 bar)	cold

- Mirror cut the design
- Weed excess material
- Place the design on the garment
- Heat apply at the conditions shown above
- Peel carrier cold

### PRODUCT HIGHLIGHTS

- easy to cut and weed
- Perfect to recreate rhinestones effect
- intense shiny colors

 **NOTE:** We highly recommend to perform a test before launching a production.

## CARE AND WASHING RECOMMENDATIONS

Washing	Ironing	Tumble dry	Dry cleaning	Storage Shelf Life	Storage Temperature	Storage Conditions	Position
Up to 40°C, inside-out	YES, inside-out	NO	NO	Up to 2 years	Between 18°C and 26°C	Away from sunlight and dust	Vertical

- Wait 24 hours after the application before the first wash
- Respect the textile recommendations
- Do not bleach or use aggressive chemical agents

 This document can be subject to variations. Updated versions are available on [www.siser.com](http://www.siser.com)  
For further information, please contact our sales office: [info@siser.it](mailto:info@siser.it)



Siser s.r.l.  
Viale della Tecnica, 18  
36100 Vicenza - Italy

Tel. +39 0444.287960  
Fax +39 0444.287959  
[info@siser.it](mailto:info@siser.it)  
[www.siser.com](http://www.siser.com)

r.e.a. vi 171856  
reg. imp. vi n° 14971  
c.s. € 103.300 i.v.  
p.iva 01591490246



Management System  
ISO 9001:2015  
ISO 14001:2015  
[www.tuv.com](http://www.tuv.com)  
ID 9105027868

